

Airpura

AIR PURIFIERS



P600

VOCS AND CHEMICALS

PHOTOCATALYTIC OXIDATION
COMBINED WITH AIRPURA'S
HIGH EFFICIENCY AIR FILTRATION

THE AIRPURA P600
Available in White / Black / Cream

THE AIRPURA LIMITED WARRANTY
5 years parts / 10 years labor

The **P600** offers the most effective airborne chemical, odor and VOC abatement available today together with suppression of microorganisms and particle filtration

- ▶ **THE P600 USES THE LATEST DISCOVERIES IN NANO-TECHNOLOGY**, developed by space research laboratories, to deliver a new and speedy airborne chemical abatement process.
- ▶ **THE TITANCLEAN™ TITANIUM DIOXIDE PHOTO-CATALYTIC OXIDIZER** dramatically increases the range of dangerous airborne chemicals that can be neutralized safely and effectively.
- ▶ **TITANCLEAN™ TITANIUM DIOXIDE (TiO2) COATING IN CONJUNCTION** with the UV light, creates an oxidizing process that instantly breaks molecular bonds and reduces airborne chemicals to smaller safer compounds, until only carbon dioxide and water vapor are left.
- ▶ **THE NEW TITANCLEAN PHOTOCATALYTIC OXIDIZER** is combined with Airpura's **18lb Activated Carbon** bed, **true Hepa Filter** and **20 watt UV Germicidal Lamp** to deliver the most complete air cleaning system available today.

EFFECTIVE FOR:

Formaldehyde	Molds, mycotoxins
Radon	PCBs
Ammonia	Trichlorophenol
Mercury vapor	Sulfur oxides
Benzene	Toluene
Aldehydes, pesticides	Nitrous oxide
Butanol	Chloroform
Carbon monoxide	Dioxane
Exhaust fumes	Chlorotoluene

LONG LASTING FILTERS

TitanClean reflectors last for 20 months depending on use

Carbon filters typically last up to 2 years depending on use

Hepa filters typically last 5 years in regular use.

Pre-filters can be vacuumed from the exterior of the unit and should be changed every 12 months depending on use

UV Germicidal lamps will be effective for up to 15,000 hours

PROTECT YOURSELF WITH AIRPURA'S SAFE EFFICIENT FILTRATION




TECHNICAL SPECIFICATIONS

THE AIRPURA TITANCLEAN™ REFLECTOR

- ▶ The TitanClean Reflector provides a large amount of TiO2 coated surface area (115% of the width of the UV lamp)
- ▶ The angled reflector design maximizes the range of photo-catalytic oxidation within the filter chamber and increases the germicidal effect of the lamp.
- ▶ The UV germicidal lamp maintains 98% of its direct irradiation intensity due to the interior position of the TitanClean reflector
- ▶ The location of the TitanClean reflector and the UV light in the center of the filter chamber allows them to work in concert with the HEPA filter.
- ▶ Particulate pollution is stopped by the Hepa filter before reaching the reflector. This keeps the coated surface cleaner and more effective.
- ▶ The diffusion of the germicidal dosage from the UV lamp is enhanced in the confined chamber.
- ▶ Contact time of airborne chemicals is increased as they slow down passing through the Hepa.
- ▶ The TitanClean Catalytic Oxidizer combined with the 18lb Activated Carbon filter offers the most complete airborne chemical and VOC abatement available today



The TitanClean reflector positioned in the center of the filter chamber



TITANCLEAN™

Photocatalytic Oxidization reflector US patent #29249549 Titanium Dioxide (TiO2) coated reflector surface

UV GERMICIDAL LAMP

20 watts. 30,000 um per cm² sec

ODOR & CHEMICAL FILTRATION

18 lbs activated carbon
13"H x 13.25"OD x 9"ID

CARBON BED

2" deep x 570 sq" surface

PARTICLE REMOVAL

40 sq ft true HEPA (Measured 1 side only)
10 pleats per inch
Pleats warm rolled with separators

AIR FLOW 560 CFM

More cfm than any other homen unit available

PRE-FILTER

570 sq in x 1 in deep

HOUSING

Powder coat steel

SIZE

23" x 15"

WEIGHT

45lbs total

VOLTAGE OPTIONS

115 or 220 volts

WATTS

120 on high / 40 on low

SOUND LEVEL

28.1 db on low (at 6 feet)
62.3 db on high (560 cfm)
(Room level 25.1 db)

ETL CERTIFIED

Conforms to ANSI / UL 507 and CSA C22.2 no 113

TITANIUM DIOXIDE PHOTOCATALYTIC OXIDIZATION

- ▶ Developed and used in space technology laboratories for both air and water purification the Photocatalytic Oxidation (PCO) process is simple and elegant.
- ▶ A metal surface coated with a metal oxide is irradiated with UV light to produce hydroxyl radicals and super-oxide ions.
- ▶ The hydroxyl radicals and super-oxide ions break the molecular bonds of chemicals they come into contact with and slice them into smaller compounds, that are further broken down until only carbon dioxide and water vapor are left.
- ▶ For maximum efficiency, the process requires a sufficient surface area of reflective metal coated with a metal oxide to be positioned at a critical distance from the UV lamp while still allowing a good flow of air to bring the airborne chemicals into contact with the resulting hydroxyl radicals and super-oxide ions.

YOUR AIRPURA™ DEALER



TRUE HEPA FILTERS

The Airpura **P600+** model features a premium titanium dioxide coated surface area. The specially coated Hepa filter offers an additional 3 times the photocatalytic capacity to deal with especially heavy concentrations of airborne chemicals.

THE MOST COMPLETE CHEMICAL AND VOC FILTRATION AVAILABLE TODAY